





WDYN856D Washer-dryer User Guide

instore


600

Machine Layout

Detergent Dispenser



Control Panel



Note: for detailed operational and maintenance instructions, please refer to the user manual provided with your appliance.

Programme Guide

Programme	Fabric Type	Water Temp Recommended (C°)	Water Temp MAX (C°)	Spin Speed MAX (RPM)	Max Load Size (kg)	Max Dry Load (kg)	Length of Programme			Detergent		Automatic Drying Cycle		
							Short	Med	Long	2	1	High Heat	Low Heat	Not Available
Cottons + Pre		60	90	1400	8	5	01:42	02:02	02:52	✓	✓	✓		
Coloureds		40	60	1400	8	5	02:04	02:24	03:14	✓	✓	✓		
A 59'		60	60	1400	3	3	00:59	-	-	✓	✓	✓		
Synthetic		40	60	800	4	4	01:19	01:29	01:39	✓	✓	✓	✓	
Delicate		40	40	400	2.5	-	01:06	-	-	✓	✓	✓	✓	✓
Wool		40	40	800	2	-	00:59	-	-	✓	✓	✓	✓	✓
Rinse		-	-	800	-	-	00:35	-	-	✓	✓	✓	✓	
Spin		-	-	1400	-	-	00:09	-	-	-	-	✓	✓	
Drain		-	-	-	-	-	00:04	-	-	-	-	✓	✓	✓
Silk		30	30	0	1.5	-	00:56	-	-	✓	✓	✓	✓	✓
Rapid 14'-30'-44'		30	30	800	1.5	1.5	00:14	-	-	✓	✓	✓	✓	
		30	40	800	2.5	2.5	-	00:30	-	✓	✓	✓	✓	
		30	40	800	3.5	3.5	-	-	00:44	✓	✓	✓	✓	
Sports		30	30	800	2.5	2.5	01:20	-	-	✓	✓	✓	✓	
High Dry		-	-	-	-	5	-	03:50	-	-	✓	✓	✓	✓
Low Dry		-	-	-	-	4	-	02:50	-	-	✓	✓	✓	✓
Wash & Dry 59'		30	30	800	1.5	1.5	00:59	-	-	✓	✓	✓	✓	✓